


Standing lamp 1 arm



120V / 60 Hz
1x60W incandescent

Suitable for indoor use only. Maximum ambient temperature 25°C.

To prevent electric shock, match wide blade of plug to wide slot.

Smooth wire : connect to the line

Ribbed wire : connect to the neutral

If the external flexible cable or cord of this luminaire is damaged, it must be exclusively replaced by the manufacturer to avoid any hazard.

Unplug the lamp before changing the bulb.

Instructions

Standing lamp 1 arm

1. Unpack without using any cutter or scissor because of possible scratches.



2. Fit the mast to the foot.

3. Screw the screw until blocking without deforming the tube.

